

flowstar



The product is designed specifically to protect the water supply against contamination from back siphonage within the laboratory environment. The nozzle must be permanently fitted to the outlet of the laboratory water tap with Loctite 648. The fitting of this nozzle will introduce the statutory air gap.

Advice must be obtained from your local water authority to ensure compliance with current water supply (water fittings) regulations 1999.

This product is manufactured with a 1/2" BSP female inlet connection, suitable laboratory taps can be supplied on request.

This is the only **FULLY** approved AUK-3 category 5 nozzle available.